



LFF6015009010

## Trunking 60150, pure white coupler and 2 cable retainer per meter

### Technical properties

#### Connectivity

Trunking coupling Pre-equipped with couplers

#### Dimensions

Trunking height 60 mm

Trunking width 150 mm

Distance bottom-punch along trunking-direction 125 mm

Distance bottom-punch crosswise trunking-direction 85 mm

#### Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 37

#### Cover, door

Lid shape loose

#### Materials

RAL colour RAL 9010 - Pure white

Material group plastic

Type of surface treatment untreated

Transparent No

#### Cable

Internal/useful cross section 7122 mm<sup>2</sup>

#### Equipment

Number of fix dividers 0

Number of plugable separators 3

Compartment quantity 1 / 4

Cable retainers per meter 2

#### Standards

European directive RoHS voluntary compliance

#### temperatur

Ambient temperature -5...65 °C