



LFF6019007030

Trunking 60190, grey coupler and 2 cable retainer per meter

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Connectivity

Trunking coupling	Pre-equipped with couplers
-------------------	----------------------------

Dimensions

Trunking height	60 mm
Length	2000 mm
Trunking width	190 mm
Distance bottom-punch along trunking-direction	125 mm
Distance bottom-punch crosswise trunking-direction	110 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	48
Maximum number of cables (Ø 11 mm, 50% fill)	48

Cover, door

Lid shape	loose
-----------	-------

Materials

Material group	plastic
Type of surface treatment	untreated
Transparent	No

Cable

Internal/useful cross section	9060 mm ²
-------------------------------	----------------------

Equipment

Number of fix dividers	0
Number of plugable separators	3
Compartment quantity	1 / 4
Cable retainers per meter	2

Standards

Approvals	EN50085-2-1
European directive RoHS	voluntary compliance

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------

temperatur

Ambient temperature	-5...65 °C
---------------------	------------