



LFF6019007030

**Trunking 60190, grey coupler and 2 cable retainer per meter**

**Technical properties**

**Configuration**

Antibacterial treatment	No
-------------------------	----

**Connectivity**

Trunking coupling	Pre-equipped with couplers
-------------------	----------------------------

**Dimensions**

Trunking height	60 mm
Length	2000 mm
Trunking width	190 mm
Distance bottom-punch along trunking-direction	125 mm
Distance bottom-punch crosswise trunking-direction	110 mm

**Capacity**

Maximum number of cables (Ø 11 mm, 50% fill)	48
Maximum number of cables (Ø 11 mm, 50% fill)	48

**Cover, door**

Lid shape	loose
-----------	-------

**Materials**

Material group	plastic
Type of surface treatment	untreated
Transparent	No

**Cable**

Internal/useful cross section	9060 mm <sup>2</sup>
-------------------------------	----------------------

**Equipment**

Number of fix dividers	0
Number of plugable separators	3
Compartment quantity	1 / 4
Cable retainers per meter	2

**Standards**

European directive RoHs	voluntary compliance
-------------------------	----------------------

**Safety**

Impact strength	IK07
-----------------	------

**Use conditions**

---

Operating temperature

-5...60 °C

**temperatur**

---

Ambient temperature

-5...65 °C