



LFF6019009010

**Trunking 60190, pure white coupler and 2 cable retainer per meter**

**Technical properties**

**Configuration**

Antibacterial treatment No

**Connectivity**

Trunking coupling Pre-equipped with couplers

**Dimensions**

Trunking height 60 mm

Length 2000 mm

Trunking width 190 mm

Distance bottom-punch along trunking-direction 125 mm

Distance bottom-punch crosswise trunking-direction 110 mm

**Capacity**

Maximum number of cables (Ø 11 mm, 50% fill) 48

Maximum number of cables (Ø 11 mm, 50% fill) 48

**Cover, door**

Lid shape loose

**Materials**

Colour pure white

RAL colour RAL 9010 - Pure white

Material group plastic

Type of surface treatment untreated

Transparent No

**Cable**

Internal/useful cross section 9060 mm<sup>2</sup>

**Equipment**

Number of fix dividers 0

Number of plugable separators 3

Compartment quantity 1 / 4

Cable retainers per meter 2

**Standards**

Approvals EN50085-2-1

**Safety**

---

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

**Use conditions**

---

Operating temperature	-5...60 °C
-----------------------	------------

**temperatur**

---

Ambient temperature	-5...65 °C
---------------------	------------