



LFF6019009010

Trunking 60190, pure white coupler and 2 cable retainer per meter

Technical properties

Architecture

Fixing mode bottom punched

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling Pre-equipped with couplers

Dimensions

Trunking height 60 mm

Length 2000 mm

Trunking width 190 mm

Distance bottom-punch along trunking-direction 125 mm

Distance bottom-punch crosswise trunking-direction 110 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 48

Maximum number of cables (Ø 11 mm, 50% fill) 48

Cover, door

Lid shape loose

Materials

Colour pure white

RAL colour RAL 9010 - Pure white

Material PVC

Material group plastic

Type of surface treatment untreated

Transparent No

Cable

Internal/useful cross section 9060 mm²

Equipment

Number of fix dividers 0

Number of plugable separators 3

Compartment quantity 1 / 4

Standards

Approvals	EN50085-2-1
European directive RoHS	voluntary compliance

Safety

Protection index IP	IP40
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------

temperatur

Ambient temperature	-5...65 °C
---------------------	------------
