



LFF6023009010

Trunking 60230, pure white coupler and 2 cable retainer per meter

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Connectivity

Trunking coupling	Pre-equipped with couplers
-------------------	----------------------------

Dimensions

Trunking height	60 mm
Length	2000 mm
Trunking width	230 mm
Distance bottom-punch along trunking-direction	125 mm
Distance bottom-punch crosswise trunking-direction	150 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	58
Maximum number of cables (Ø 11 mm, 50% fill)	58

Cover, door

Lid shape	loose
-----------	-------

Materials

Colour	pure white
RAL colour	RAL 9010 - Pure white
Material group	plastic
Type of surface treatment	untreated
Transparent	No

Cable

Internal/useful cross section	10998 mm ²
-------------------------------	-----------------------

Equipment

Number of plugable separators	3
Compartment quantity	1 / 4
Cable retainers per meter	2

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

Use conditions

Operating temperature

-5...60 °C

temperatur

Ambient temperature

-5...65 °C