



LFF71H0999010

## 10 Extensions for support LFF71H090 pure white

### Technical properties

#### Architecture

Fixing mode	Clamping
-------------	----------

#### Compatibility

Device installation compatible format	45x45 mm
---------------------------------------	----------

#### Dimensions

Trunking height	60 mm
Length	65 mm
Trunking width	90 mm

#### Cover, door

Lid mounting	Internal
Shape of cover for wall duct	Plain

#### Materials

RAL colour	RAL 9010 - Pure white
Material	ABS
Material group	plastic
Type of surface treatment	untreated

#### Installation, mounting

Assembly	juxtaposable
----------	--------------

#### Accessories included

Fitted with	empty
-------------	-------

#### Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

#### Safety

Protection index IP	IP40
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

#### temperatur

Ambient temperature	-5...60 °C
---------------------	------------