



LFH6015109010



Technical properties

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	60 mm
Length	2000 mm
Trunking width	150 mm
Distance bottom-punch along trunking-direction	250 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	46
Maximum number of cables (Ø 11 mm, 50% fill)	46

Cover, door

Lid shape	loose
-----------	-------

Materials

RAL colour	RAL 9010 - Pure white
Material	PC-ABS
Material group	plastic
Type of surface treatment	untreated
Transparent	No

Cable

Internal/useful cross section	7300 mm ²
-------------------------------	----------------------

Equipment

Number of fix dividers	1
Number of plugable separators	0
Compartment quantity	2
Cable retainers per meter	2

temperatur

Ambient temperature	-30...90 °C
---------------------	-------------