



LFR1501509010T2



Mini flexible trunking on roll with adhesive tape LFR 15x15mm PVC in pure white

Technical properties

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 15 mm

Length 20000 mm

Trunking width 15 mm

Distance bottom-punch along trunking-direction 125 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 1

Cover, door

Lid shape hinge

Materials

RAL colour RAL 9010 - Pure white

Material group plastic

Type of surface treatment untreated

Transparent No

Cable

Internal/useful cross section 256 mm²

Equipment

Number of fix dividers 0

Number of plugable separators 0

Compartment quantity 1

Cable retainers per meter 0

Standards

European directive RoHs voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Use conditions

Operating temperature

-5...60 °C