



LFS200200VERZ



## Trunking LFS made of steel 20x20mm in pure white

### Technical properties

#### Configuration

Antibacterial treatment	No
-------------------------	----

#### Connectivity

Trunking coupling	Couplers as separate reference
-------------------	--------------------------------

#### Dimensions

Trunking height	18 mm
-----------------	-------

Length	2000 mm
--------	---------

Trunking width	19 mm
----------------	-------

Distance bottom-punch along trunking-direction	200 mm
--	--------

#### Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	1
--	---

Maximum number of cables (Ø 11 mm, 50% fill)	1
--	---

#### Cover, door

Lid shape	premounted
-----------	------------

#### Materials

Material group	steel
----------------	-------

Transparent	No
-------------	----

#### Cable

Internal/useful cross section	228 mm <sup>2</sup>
-------------------------------	---------------------

#### Equipment

Compartment quantity	1
----------------------	---

#### Standards

Approvals	EN50085-2-1
-----------	-------------

European directive RoHS	voluntary compliance
-------------------------	----------------------

#### Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----

Impact strength	IK08
-----------------	------

#### Use conditions

