



LFS200200VERZ



Trunking LFS made of steel 20x20mm in pure white

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Connectivity

Trunking coupling	Couplers as separate reference
-------------------	--------------------------------

Dimensions

Trunking height	18 mm
Length	2000 mm
Trunking width	19 mm
Distance bottom-punch along trunking-direction	200 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	1
Maximum number of cables (Ø 11 mm, 50% fill)	1

Cover, door

Lid shape	premounted
-----------	------------

Materials

Colour	zinc coated
Material	Steel
Material group	steel
Type of surface treatment	Galvanised
Transparent	No

Cable

Internal/useful cross section	228 mm ²
-------------------------------	---------------------

Equipment

Compartment quantity	1
----------------------	---

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP30
REACH conform	Yes
RoHS conform	Yes

Halogen free	Yes
--------------	-----

Use conditions

Operating temperature	-5...90 °C
-----------------------	------------