



LFS200200VERZ



Trunking LFS made of steel 20x20mm in pure white

Technical properties

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling Couplers as separate reference

Dimensions

Trunking height 18 mm

Length 2000 mm

Trunking width 19 mm

Distance bottom-punch along trunking-direction 200 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 1

Maximum number of cables (Ø 11 mm, 50% fill) 1

Cover, door

Lid shape premounted

Materials

Material Steel

Material group steel

Type of surface treatment Galvanised

Transparent No

Cable

Internal/useful cross section 228 mm²

Equipment

Compartment quantity 1

Standards

European directive RoHS voluntary compliance

Safety

Protection index IP IP30

Use conditions

Operating temperature -5...90 °C