



LFS300450VERZ



**Trunking LFS made of steel 30x45mm in galvanized**

**Technical properties**

**Configuration**

Antibacterial treatment No

**Connectivity**

Trunking coupling Couplers as separate reference

**Dimensions**

Trunking height 30 mm

Length 2000 mm

Trunking width 45 mm

Distance bottom-punch along trunking-direction 200 mm

**Capacity**

Maximum number of cables (Ø 11 mm, 50% fill) 4

Maximum number of cables (Ø 11 mm, 50% fill) 4

**Cover, door**

Lid shape loose

**Materials**

Material Steel

Material group steel

Type of surface treatment Galvanised

Transparent No

**Cable**

Internal/useful cross section 970 mm<sup>2</sup>

**Equipment**

Compartment quantity 1

**Standards**

European directive RoHS voluntary compliance

**Safety**

Protection index IP IP30

**Use conditions**

Operating temperature -5...90 °C