



LFS300450VERZ



Trunking LFS made of steel 30x45mm in galvanized

Technical properties

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling Couplers as separate reference

Dimensions

Trunking height 30 mm

Length 2000 mm

Trunking width 45 mm

Distance bottom-punch along trunking-direction 200 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 4

Maximum number of cables (Ø 11 mm, 50% fill) 4

Cover, door

Lid shape loose

Materials

Material group steel

Transparent No

Cable

Internal/useful cross section 970 mm²

Equipment

Compartment quantity 1

Standards

Approvals EN50085-2-1

European directive RoHS voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Impact strength IK08

Use conditions

