



LFS4006009010



Trunking LFS made of steel 40x60mm in pure white

Technical properties

Architecture

Fixing mode bottom punched

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling Couplers as separate reference

Dimensions

Trunking height 40 mm

Length 2000 mm

Trunking width 60 mm

Distance bottom-punch along trunking-direction 250 mm

Distance bottom-punch crosswise trunking-direction 40 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 7

Maximum number of cables (Ø 11 mm, 50% fill) 7

Cover, door

Lid shape loose

Materials

Colour pure white

RAL colour RAL 9010 - Pure white

Material Steel

Material group steel

Type of surface treatment Painted

Transparent No

Cable

Internal/useful cross section 1700 mm²

Equipment

Number of fix dividers 0

Number of plugable separators 0

Compartment quantity 1

Standards

Approvals	EN50085-2-1
European directive RoHS	voluntary compliance

Safety

Protection index IP	IP30
REACH conform	Yes
RoHS conform	Yes
Impact strength	IK08

Use conditions

Operating temperature	-5...90 °C
-----------------------	------------
