



LFS400600VERZ



Trunking LFS made of steel 40x60mm galvanized

Technical properties

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling Couplers as separate reference

Dimensions

Trunking height 40 mm

Length 2000 mm

Trunking width 60 mm

Distance bottom-punch along trunking-direction 250 mm

Distance bottom-punch crosswise trunking-direction 40 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 7

Maximum number of cables (Ø 11 mm, 50% fill) 7

Cover, door

Lid shape loose

Materials

Material Steel

Material group steel

Type of surface treatment Galvanised

Transparent No

Cable

Internal/useful cross section 1700 mm²

Equipment

Compartment quantity 1

Cable retainers per meter 2

Standards

European directive RoHS voluntary compliance

Safety

Protection index IP IP30

Use conditions

Operating temperature

-5...90 °C