



LFS600600VERZ



Trunking LFS made of steel 60x60mm galvanized

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Connectivity

Trunking coupling	Couplers as separate reference
-------------------	--------------------------------

Dimensions

Trunking height	60 mm
Length	2000 mm
Trunking width	60 mm
Distance bottom-punch along trunking-direction	250 mm
Distance bottom-punch crosswise trunking-direction	40 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	12
Maximum number of cables (Ø 11 mm, 50% fill)	12

Cover, door

Lid shape	loose
-----------	-------

Materials

Colour	zinc coated
Material	Steel
Material group	steel
Type of surface treatment	Galvanised
Transparent	No

Cable

Internal/useful cross section	2860 mm ²
-------------------------------	----------------------

Equipment

Compartment quantity	1
Cable retainers per meter	2

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP30
---------------------	------

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Use conditions	
Operating temperature	-5...90 °C