



LFS600600VERZ



## Trunking LFS made of steel 60x60mm galvanized

### Technical properties

#### Configuration

Antibacterial treatment	No
-------------------------	----

#### Connectivity

Trunking coupling	Couplers as separate reference
-------------------	--------------------------------

#### Dimensions

Trunking height	60 mm
Length	2000 mm
Trunking width	60 mm
Distance bottom-punch along trunking-direction	250 mm
Distance bottom-punch crosswise trunking-direction	40 mm

#### Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	12
Maximum number of cables (Ø 11 mm, 50% fill)	12

#### Cover, door

Lid shape	loose
-----------	-------

#### Materials

Material group	steel
Transparent	No

#### Cable

Internal/useful cross section	2860 mm <sup>2</sup>
-------------------------------	----------------------

#### Equipment

Compartment quantity	1
Cable retainers per meter	2

#### Standards

Approvals	EN50085-2-1
European directive RoHS	voluntary compliance

#### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

**Use conditions**

---

Operating temperature

-5...90 °C