



LFS6010009010



Trunking LFS made of steel 60x100mm in pure white

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Connectivity

Trunking coupling	Couplers as separate reference
-------------------	--------------------------------

Dimensions

Trunking height	60 mm
Length	2000 mm
Trunking width	100 mm
Distance bottom-punch along trunking-direction	250 mm
Distance bottom-punch crosswise trunking-direction	70 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	21
Maximum number of cables (Ø 11 mm, 50% fill)	21

Cover, door

Lid shape	loose
-----------	-------

Materials

RAL colour	RAL 9010 - Pure white
Material	Steel
Material group	steel
Type of surface treatment	Painted
Transparent	No

Cable

Internal/useful cross section	5025 mm²
-------------------------------	----------

Equipment

Number of fix dividers	0
Number of plugable separators	1
Compartment quantity	1 / 2
Cable retainers per meter	2

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety	
Protection index IP	IP30
REACH conform	Yes
RoHS conform	Yes
Use conditions	
Operating temperature	-5...90 °C