


LFS601000VERZ



Trunking LFS made of steel 60x100mm galvanized

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Connectivity

Trunking coupling	Couplers as separate reference
-------------------	--------------------------------

Dimensions

Trunking height	60 mm
Length	2000 mm
Trunking width	100 mm
Distance bottom-punch along trunking-direction	250 mm
Distance bottom-punch crosswise trunking-direction	70 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	21
Maximum number of cables (Ø 11 mm, 50% fill)	21

Cover, door

Lid shape	loose
-----------	-------

Materials

Material group	steel
Transparent	No

Cable

Internal/useful cross section	5025 mm ²
-------------------------------	----------------------

Equipment

Number of plugable separators	1
Compartment quantity	1 / 2
Cable retainers per meter	2

Standards

Approvals	EN50085-2-1
European directive RoHS	voluntary compliance

Safety

Halogen free	Yes
Impact strength	IK08

Use conditions

Operating temperature

-5...90 °C