


LFS601000VERZ



Trunking LFS made of steel 60x100mm galvanized

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Connectivity

Trunking coupling	Couplers as separate reference
-------------------	--------------------------------

Dimensions

Trunking height	60 mm
Length	2000 mm
Trunking width	100 mm
Distance bottom-punch along trunking-direction	250 mm
Distance bottom-punch crosswise trunking-direction	70 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	21
Maximum number of cables (Ø 11 mm, 50% fill)	21

Cover, door

Lid shape	loose
-----------	-------

Materials

Material	Steel
Material group	steel
Type of surface treatment	Galvanised
Transparent	No

Cable

Internal/useful cross section	5025 mm ²
-------------------------------	----------------------

Equipment

Number of pluggable separators	1
Compartment quantity	1 / 2
Cable retainers per meter	2

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP30
---------------------	------

Use conditions

Operating temperature

-5...90 °C