



LFS601500VERZ



Trunking LFS made of steel 60x150mm galvanized

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Connectivity

Trunking coupling	Couplers as separate reference
-------------------	--------------------------------

Dimensions

Trunking height	60 mm
Length	2000 mm
Trunking width	150 mm
Distance bottom-punch along trunking-direction	250 mm
Distance bottom-punch crosswise trunking-direction	110 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	29
Maximum number of cables (Ø 11 mm, 50% fill)	29

Cover, door

Lid shape	loose
-----------	-------

Materials

Material group	steel
Transparent	No

Cable

Internal/useful cross section	7000 mm ²
-------------------------------	----------------------

Equipment

Number of plugable separators	2
Compartment quantity	1 / 3
Cable retainers per meter	2

Standards

Approvals	EN50085-2-1
European directive RoHS	voluntary compliance

Safety

Halogen free	Yes
Impact strength	IK08

Use conditions

Operating temperature

-5...90 °C