



LFS6020009010



Trunking LFS made of steel 60x200mm in pure white

Technical properties

Connectivity

Trunking coupling Couplers as separate reference

Dimensions

Trunking height 60 mm

Length 2000 mm

Trunking width 200 mm

Distance bottom-punch along trunking-direction 250 mm

Distance bottom-punch crosswise trunking-direction 150 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 41

Cover, door

Lid shape loose

Materials

RAL colour RAL 9010 - Pure white

Material group steel

Transparent No

Cable

Internal/useful cross section 9770 mm²

Equipment

Number of fix dividers 0

Number of plugable separators 3

Compartment quantity 1 / 4

Cable retainers per meter 2

Standards

Approvals EN50085-2-1

European directive RoHS voluntary compliance