



LFS602000VERZ



## Trunking LFS made of steel 60x200mm galvanized

### Technical properties

#### Connectivity

Trunking coupling	Couplers as separate reference
-------------------	--------------------------------

#### Dimensions

Trunking height	60 mm
Length	2000 mm
Trunking width	200 mm
Distance bottom-punch along trunking-direction	250 mm
Distance bottom-punch crosswise trunking-direction	150 mm

#### Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	41
--	----

#### Cover, door

Lid shape	loose
-----------	-------

#### Materials

Colour	zinc coated
Material	Steel
Material group	steel
Type of surface treatment	Galvanised
Transparent	No

#### Cable

Internal/useful cross section	9770 mm <sup>2</sup>
-------------------------------	----------------------

#### Equipment

Number of fix dividers	0
Number of plugable separators	3
Compartment quantity	1 / 4
Cable retainers per meter	2

#### Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------