



LFS602000VERZ



Trunking LFS made of steel 60x200mm galvanized

Technical properties

Connectivity

Trunking coupling Couplers as separate reference

Dimensions

Trunking height	60 mm
Length	2000 mm
Trunking width	200 mm
Distance bottom-punch along trunking-direction	250 mm
Distance bottom-punch crosswise trunking-direction	150 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 41

Cover, door

Lid shape loose

Materials

Material	Steel
Material group	steel
Type of surface treatment	Galvanised
Transparent	No

Cable

Internal/useful cross section 9770 mm²

Equipment

Number of fix dividers	0
Number of plugable separators	3
Compartment quantity	1 / 4
Cable retainers per meter	2

Standards

European directive RoHS voluntary compliance