



LFS602000VERZ



**Trunking LFS made of steel 60x200mm galvanized**

**Technical properties**

**Connectivity**

Trunking coupling	Couplers as separate reference
-------------------	--------------------------------

**Dimensions**

Trunking height	60 mm
Length	2000 mm
Trunking width	200 mm
Distance bottom-punch along trunking-direction	250 mm
Distance bottom-punch crosswise trunking-direction	150 mm

**Capacity**

Maximum number of cables (Ø 11 mm, 50% fill)	41
--	----

**Cover, door**

Lid shape	loose
-----------	-------

**Materials**

Material group	steel
Transparent	No

**Cable**

Internal/useful cross section	9770 mm <sup>2</sup>
-------------------------------	----------------------

**Equipment**

Number of fix dividers	0
Number of plugable separators	3
Compartment quantity	1 / 4
Cable retainers per meter	2

**Standards**

Approvals	EN50085-2-1
European directive RoHs	voluntary compliance