



LR602

## Fuse carrier 2P 50A 690V L51 3M

### Technical properties

#### Architecture

Number of poles	2 P
-----------------	-----

#### Configuration

Number of modules	3
-------------------	---

#### Electric current

Rated current	50 A
---------------	------

#### Fuse

CharactFuse	gG ; aM
-------------	---------

#### Dimensions

Depth of installed product	93 mm
----------------------------	-------

Height of installed product	107 mm
-----------------------------	--------

Width of installed product	52.5 mm
----------------------------	---------

#### Power

Total power loss under IN	12.5 W
---------------------------	--------

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

#### Use conditions

Operating temperature	-5...40 °C
-----------------------	------------

Storage/transport temperature	-25...80 °C
-------------------------------	-------------