



LR603

Fuse carrier 3P 50A 690V L51 4.5M

Technical properties

Architecture

Number of poles	3 P
Type of pole	3 P

Configuration

Number of modules	4.5
-------------------	-----

Electric current

Rated current	50 A
---------------	------

Fuse

CharactFuse	gG ; aM
-------------	---------

Dimensions

Depth of installed product	93 mm
Height of installed product	107 mm
Width of installed product	78.75 mm

Power

Total power loss under IN	18.88 W
---------------------------	---------

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-5...40 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Storage/transport temperature	-25...80 °C