



M1659TRAN



M 1659 Transparent Mini-Snap 7,5-10

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	11 mm
Length	2000 mm
Trunking width	11 mm

Cover, door

Lid shape	none
-----------	------

Materials

Colour	colourless
Material	PVC
Material group	plastic
Type of surface treatment	untreated
Transparent	Yes

Cable

Internal/useful cross section	100 mm ²
-------------------------------	---------------------

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------

temperatur

Ambient temperature	-5...65 °C
---------------------	------------