



Divider H: 40 mm

Technical properties

Architecture

Fixing mode Clamping

Dimensions

Trunking height 40 mm

Length 2000 mm

Materials

Material group plastic

Type of surface treatment untreated

Standards

European directive RoHS voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

M2024

