



M2026



partition LF H60

Technical properties

Architecture

Fixing mode Clipped

Configuration

Module 1 Gang

Compatibility

Product compatibility LF (150, 190, 230)

Dimensions

Trunking height 60 mm

Length 2000 mm

Materials

Material group plastic

Type of surface treatment untreated

Standards

European directive RoHS voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No