



M53037030



End cap, FB 80130, grey

Technical properties

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 82 mm

Trunking width 130 mm

Materials

Material group plastic

Type of surface treatment untreated

Standards

European directive RoHs voluntary compliance

Safety

REACH conform No

RoHS conform Yes

Halogen free No

Impact strength IK07

Use conditions

Operating temperature -5...60 °C

temperatur

Ambient temperature -5...65 °C