



M53037030



End cap, FB 80130, grey

Technical properties

Architecture

Fixing mode Screwed

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 82 mm

Trunking width 130 mm

Materials

Colour stone grey

Material group plastic

Type of surface treatment untreated

Standards

European directive RoHS voluntary compliance

Safety

Protection index IP IP20

Impact strength IK07

Use conditions

Operating temperature -5...60 °C

temperatur

Ambient temperature -5...65 °C