



M53967030



T and X piece, LF 30060, grey

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Dimensions

Trunking height	30 mm
-----------------	-------

Trunking width	57 mm
----------------	-------

Measure a	170 mm
-----------	--------

Cover, door

Lid with softlip	-
------------------	---

Materials

Colour	stone grey
--------	------------

Material group	plastic
----------------	---------

Type of surface treatment	untreated
---------------------------	-----------

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

Impact strength	IK07
-----------------	------

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------

temperatur

Ambient temperature	-5...65 °C
---------------------	------------