



M54069010



T-piece halogen free for LFxxx 40x60mm pure white

Technical properties

Architecture

Fixing mode Hold in position thanks to lid

Configuration

Antibacterial treatment No

Dimensions

Trunking height 40 mm

Trunking width 57 mm

Measure a 170 mm

Height 40 mm

Width 57 mm

Cover, door

Lid with softlip -

Materials

Colour pure white

RAL colour RAL 9010 - Pure white

Material ABS

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching Without base punching

Accessories included

Accessory configuration Moulded

Standards

Approvals EN50085-2-1

European directive RoHS voluntary compliance

Safety

Impact strength IK07

Use conditions

Operating temperature -5...90 °C

temperatur

Ambient temperature -5...65 °C