



M5429



Cable retainer, LF/LFF/LFP B=110mm

Technical properties

Architecture

Fixing mode Clipped

Dimensions

Trunking height 60 mm

Trunking width 110 mm

Materials

Colour black

Material PC-ABS

Material group plastic

Type of surface treatment untreated

Equipment

Cable retainer implementation Front pivoting and sliding

Standards

European directive RoHs voluntary compliance