



M54669010



T-piece halogen free for LFxxx 60x90mm pure white

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Dimensions

Trunking height	60 mm
-----------------	-------

Trunking width	90 mm
----------------	-------

Measure a	190 mm
-----------	--------

Cover, door

Lid with softlip	-
------------------	---

Materials

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Material	PC-ABS
----------	--------

Material group	plastic
----------------	---------

Type of surface treatment	untreated
---------------------------	-----------

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

Impact strength	IK07
-----------------	------

Use conditions

Operating temperature	-5...90 °C
-----------------------	------------

temperatur

Ambient temperature	-5...65 °C
---------------------	------------