



M55027030



## External corner, LF/FB 60110, grey

### Technical properties

#### Configuration

Antibacterial treatment	No
-------------------------	----

#### Compatibility

Product compatibility	LF, LFF
-----------------------	---------

#### Connectivity

Trunking coupling	without coupler
-------------------	-----------------

#### Dimensions

Trunking height	61 mm
-----------------	-------

Trunking width	110 mm
----------------	--------

Measure a	70 mm
-----------	-------

#### Cover, door

Lid with softlip	-
------------------	---

#### Materials

Material group	plastic
----------------	---------

Type of surface treatment	untreated
---------------------------	-----------

#### Installation, mounting

Base punching	Without base punching
---------------	-----------------------

#### Settings

Angle range	90 °
-------------	------

#### Accessories included

Accessory configuration	Moulded
-------------------------	---------

#### Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

#### Safety

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Impact strength	IK07
-----------------	------

#### Use conditions

Operating temperature	-5...60 °C
-----------------------	------------