



M55027030



External corner, LF/FB 60110, grey

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

Product compatibility	LF, LFF
-----------------------	---------

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	61 mm
-----------------	-------

Trunking width	110 mm
----------------	--------

Measure a	70 mm
-----------	-------

Cover, door

Lid with softlip	-
------------------	---

Materials

Material group	plastic
----------------	---------

Type of surface treatment	untreated
---------------------------	-----------

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Settings

Angle range	90 °
-------------	------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Impact strength	IK07
-----------------	------

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------