



M55057030



Flat corner, LF/FB60110, grey

Technical properties

Configuration

Antibacterial treatment No

Compatibility

Product compatibility LF, LFF

Dimensions

Trunking height 61 mm

Trunking width 110 mm

Measure a 140 mm

Cover, door

Lid with softlip -

Materials

Type of surface treatment untreated

Installation, mounting

Base punching Without base punching

Settings

Angle range 90 °

Accessories included

Accessory configuration Moulded

Safety

REACH conform No

RoHS conform Yes

Halogen free No

Impact strength IK07

Use conditions

Operating temperature -5...60 °C