



M55059010



Flat corner, LF/FB60110, pure white

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

Product compatibility	LF, LFF, FB
-----------------------	-------------

Dimensions

Trunking height	61 mm
Trunking width	110 mm
Measure a	140 mm

Cover, door

Lid with softlip	-
------------------	---

Materials

RAL colour	RAL 9010 - Pure white
Material	PVC
Type of surface treatment	untreated

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Settings

Angle range	90 °
-------------	------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

Use conditions

Operating temperature	-5...90 °C
-----------------------	------------

temperatur

Ambient temperature	-5...65 °C
---------------------	------------