



M55069010



**T-piece halogen free for LFxxx/FB 60x110mm pure white**

**Technical properties**

**Configuration**

Antibacterial treatment No

**Compatibility**

Product compatibility LF, FB

**Dimensions**

Trunking height 61 mm

Trunking width 110 mm

Measure a 190 mm

**Cover, door**

Lid with softlip -

**Materials**

RAL colour RAL 9010 - Pure white

Material group plastic

Type of surface treatment untreated

**Installation, mounting**

Base punching Without base punching

**Accessories included**

Accessory configuration Moulded

**Standards**

European directive RoHS voluntary compliance

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free No

Impact strength IK07

**Use conditions**

Operating temperature -5...90 °C

**temperatur**

Ambient temperature -5...60 °C