



M55117030



Internal corner, FB 60130, grey

Technical properties

Configuration

Antibacterial treatment No

Compatibility

Product compatibility LF, LFF

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 61 mm

Trunking width 130 mm

Measure a 130 mm

Cover, door

Lid with softlip No

Materials

Colour stone grey

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching Without base punching

Settings

Angle range 90 °

Accessories included

Accessory configuration Moulded

Standards

European directive RoHS voluntary compliance

Safety

Protection index IP IP30

Impact strength IK07

Use conditions

Operating temperature -5...60 °C