



M55117030



Internal corner, FB 60130, grey

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

Product compatibility	LF, LFF
-----------------------	---------

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	61 mm
Trunking width	130 mm
Measure a	130 mm

Cover, door

Lid with softlip	No
------------------	----

Materials

Material group	plastic
Type of surface treatment	untreated

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Settings

Angle range	90 °
-------------	------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------