



M55137030



## End cap, FB 60130, grey

### Technical properties

#### Architecture

Fixing mode	Clamping and screwable
-------------	------------------------

#### Configuration

Antibacterial treatment	No
-------------------------	----

#### Compatibility

Product compatibility	LF/FB
-----------------------	-------

#### Connectivity

Trunking coupling	without coupler
-------------------	-----------------

#### Dimensions

Trunking height	61 mm
-----------------	-------

Trunking width	130 mm
----------------	--------

#### Materials

Material group	plastic
----------------	---------

Type of surface treatment	untreated
---------------------------	-----------

#### Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

#### Safety

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Impact strength	IK07
-----------------	------

#### Use conditions

Operating temperature	-5...60 °C
-----------------------	------------