



M55157030



**Flat corner, FB 60130, grey**

**Technical properties**

**Configuration**

Antibacterial treatment No

**Compatibility**

Product compatibility LF, LFF

**Dimensions**

Trunking height 61 mm

Trunking width 130 mm

Measure a 160 mm

**Cover, door**

Lid with softlip No

**Materials**

Type of surface treatment untreated

**Installation, mounting**

Base punching Without base punching

**Settings**

Angle range 90 °

**Accessories included**

Accessory configuration Moulded

**Safety**

REACH conform No

RoHS conform Yes

Halogen free No

Impact strength IK07

**Use conditions**

Operating temperature -5...60 °C