



M55157030



## Flat corner, FB 60130, grey

### Technical properties

#### Configuration

Antibacterial treatment	No
-------------------------	----

#### Compatibility

Product compatibility	LF, LFF
-----------------------	---------

#### Dimensions

Trunking height	61 mm
-----------------	-------

Trunking width	130 mm
----------------	--------

Measure a	160 mm
-----------	--------

#### Cover, door

Lid with softlip	No
------------------	----

#### Materials

Colour	stone grey
--------	------------

Type of surface treatment	untreated
---------------------------	-----------

#### Installation, mounting

Base punching	Without base punching
---------------	-----------------------

#### Settings

Angle range	90 °
-------------	------

#### Accessories included

Accessory configuration	Moulded
-------------------------	---------

#### Safety

Protection index IP	IP30
---------------------	------

Impact strength	IK07
-----------------	------

#### Use conditions

Operating temperature	-5...60 °C
-----------------------	------------