



M55219010



internal corner halogen free for trunking system LFxxx/FB 60x150mm pure white

Technical properties

Configuration

Antibacterial treatment No

Compatibility

Product compatibility LF, LFF, FB

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 61 mm

Trunking width 150 mm

Measure a 130 mm

Cover, door

Lid with softlip -

Materials

RAL colour RAL 9010 - Pure white

Material PC-ABS

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching Without base punching

Settings

Angle range 90 °

Accessories included

Accessory configuration Moulded

Standards

European directive RoHS voluntary compliance

Safety

Impact strength IK07

Use conditions

Operating temperature -5...90 °C

temperatur

