




M55227030



external corner halogen free for trunking system LFxxx/FB 60x150mm pearl grey

Technical properties

Configuration

Antibacterial treatment No

Compatibility

Product compatibility LF, LFF

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 61 mm

Trunking width 150 mm

Measure a 70 mm

Cover, door

Lid with softlip -

Materials

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching Without base punching

Settings

Angle range 90 °

Accessories included

Accessory configuration Moulded

Standards

European directive RoHS voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Impact strength IK07

Use conditions

Operating temperature -5...60 °C