



M55239010



endcap halogen free for trunking system LFxxx/FB 60x150mm pure white

Technical properties

Architecture

Fixing mode Clamping and screwable

Configuration

Antibacterial treatment No

Compatibility

Product compatibility LF/FB

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 61 mm

Trunking width 150 mm

Materials

RAL colour RAL 9010 - Pure white

Material group plastic

Type of surface treatment untreated

Standards

European directive RoHs voluntary compliance

Safety

REACH conform No

RoHS conform Yes

Impact strength IK07

Use conditions

Operating temperature -5...90 °C